Electronic Solutions for the 21st Century

ICM-HDIO-08P

High Denisty I/O Expander - 8 In / 8 Out DC Commoned



PRODUCT DESCRIPTION:

The ICM-HDIO-08P is designed for direct connection with any of the Divelbiss Bear Bones, High Density Bear Bones, Boss Bear, Boss32, Universal Control Panel (UCP) and Universal Machine Controller (UMC) product families.

PRODUCT FEATURES:

- Quickly Connects using ICM-HDCA Series Cables
- Optically Isolated I/O points
- Reverse polarity protection
- Small size and light weight
- Mounts on industry standard DIN rail type NS31 or NS35
- Addressable via programming jumpers
- Detatachable Input / Output blocks
- Polarized and locking data and power bus connections
- LED monitoring of I/O status
- Engineered to meet NEMA part ICS 3-304
- DC Commoned Inputs & Outputs
- Fused Outputs with Spare Fuse & Fuse Tester



Table of Contents

Input Specifications	2
Typical Input Connections & Circuit Diagrams	
Output Specifications	3
Typical Output Connections & Circuit Diagrams	
Addressing I/O Points	
Power Consumption	
Data Connections	
Mounting & Dimensions	
Connectivity Diagrams	
	5

----WARNING----

The ICM-HDIO-08P, as with other solid state control devices, must not be used in applications which would be hazardous to personnel in the event of failure of the controller. Precautions must be taken to provide mechanical and/or electrical safeguards external to the controller. This device is **NOT APPROVED** for domestic or human medical use.

DIVELBISS CORPORATION 9778 MT. GILEAD RD. FREDERICKTOWN, OH 43019 (800) 245-2327 Document #: ds2000-0008

Revision: A

Page 1 of 5

http://www.divelbiss.com divelbiss@divelbiss.com



INPUT SPECIFICATIONS:

Channels: 8

Input Voltage: 10-32 VDC

Turn on Level: 8VDC @ 2.3mADC Minimum

Turn off Level: 2.5VDC @ 0.05mADC Maximum

Turn on Time:

with debounce: 30mSec Nominal @ 24VDC

without debounce: 2μSec Nominal @ 24VDC

Turn off Time:

with debounce: 30mSec Nominal @ 24VDC without debounce: 30µSec Nominal @ 24VDC

Isolation (Input to Logic Level): 3.6KV Minimum for 1 Second **Isolation** (Interchannel): 3KV Minimum for 1 Second


Static Input Resistance: 2KOhm Nominal


Input Types: Sink
Optical Isolation: Yes

LED Status Indicators: Yes

TYPICAL INPUT CIRCUIT DIAGRAMS

Typical ICM-HDIO-08P Input Circuit





Sinking Input Circuit

Document Number: ds2000-0008



OUTPUT SPECIFICATIONS:

# Channels:	8
-------------	---

Nominal Source Voltage: 24 VDC

Max Source Voltage: 30 VDC

"On" State Voltage Drop: 2.4VDC Maximum @ 1 Amp

Load Current:

Minimum: .5mADC*

Maximum: 1 Amp*

Turn On Time: 10 μSec Maximum

Turn Off Time: 1mSec Maximum

Surge Current: 2 Amp Maximum for 1 Second*

Isolation (Output to Logic Level): 3.6KV Minimum for 1 Second

Isolation (Interchannel): 3KV Minimum for 1 Second

Output Types: Sink


Optical Isolation: Yes
LED Status Indicators: Yes


Fused: Yes

"Off" State Leakage Current: 100 µADC Max. @ 30 VDC*

TYPICAL OUTPUT CIRCUIT DIAGRAMS

Typical ICM-HDIO-08P Output Circuit





Sinking Output Circuit

Document Number: ds2000-0008

Page 3 of 5

web: http://www.divelbiss.com email: divelbiss@divelbiss.com

DIVELBISS CORPORATION 9778 MT. GILEAD RD. FREDERICKTOWN, OH 43019 (800) 245-2327

Specifications Subject to change without notice

^{* @ 0-55} Degrees C.



Addressing I/O Points

The I/O is addressed into "pages". Each "page" represents 16 inputs and 16 outputs. The HDIO-08P addresses a "half page". It may be addressed to any page 0 through 7. Limitations apply when connected to a Bear Bones, Baby Bear Bones or High Density Bear Bones CPU. When connected to these CPUs, the HDIO may NOT be addressed on "Page 1". "Page" selection is done via programming shunts "Address Selector(s) 1,2,4,8". See page selection to the right for more details. *Note: Some models may only use selectors 1,2,4. Page 6 cannot be address when HDIO is used with PIC-AB-01.

Card Page Address	Card Paging Shunts (Address Selector)	U/L Selector Lower L	DIN/ DOUT 8 I/O Cards	DIN/ DOUT 16 I/O Cards	Card Page Address	Card Paging Shunts (Address Selector) 8 4 2 1	U/L Selector Lower	DIN/ DOUT 8 I/O Cards	DIN/ DOUT 16 I/O Cards
0	1111	U 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	0-7 8-15	0-15	8		U D L U	128-135 136-143	128-143
1		U 0 L 0 L 0	16-23 24-31	16-31	9		U 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	144-151 152-159	144-159
2		U 0 L 0 U 0 L 0	32-39 40-47	32-47	10		U 0	160-167 168-175	160-175
3		U 0	48-55 56-63	48-63	11		U 0	176-183 184-191	176-191
4		U 0 L 0 L 0	64-71 72-79	64-79	12		U 0	192-199 200-207	192-207
5		U 0	80-87 88-95	80-95	13		UB L	208-215 216-223	208-223
6		U	96-103 104-111	96-111	14		U 0	224-231 232-239	224-239
7		U © L • U •	112-119 120-127	112-127	15	000	U 0 L • U • L 0	240-247 248-255	240-255

Power Consumption

Power Input Standby: +5VDC @ 2mA Maximum

Power Input Origin: Controller/Aux Powersupply via Cable 3

I/O Point Power Consumption:

Activated Inputs: 1.7mA each input point (additional)
Activated Outputs: 8mA each output point (additional)

DATA CONNECTIONS

The data is received from the controller via a ribbon cable connected to Conn6. The controller provides all the addressing, data and selection signals necessary for complete operation.

MOUNTING & DIMENSIONS

Mounting Type: Industry Standard DIN Rail NS 31 or NS 35

Dimensions:

Width: 4.25 Inches
Length: 4.225 Inches

Depth: 1.7 Inches (including din rail mounting feet)

Document Number: ds2000-0008

Page 4 of 5


web: http://www.divelbiss.com email: divelbiss@divelbiss.com

FREDERICKTOWN, OH 43019 (800) 245-2327

DIVELBISS CORPORATION

9778 MT. GILEAD RD.





Maximum Recommended wire size is 14 AWG.

CABLING

The ICM-HDIO-08P connects to any of the Divelbiss controllers using standard cable sets. See below for proper cable. Custom Cabling is also available.

Connect	to	В	oss32,	UCP,	UMC
	an	d	HDCPI	I	

ICM-HDCA-01 Connects 1 Expander (9")
ICM-HDCA-02 Connects 2 Expander (18")
ICM-HDCA-03 Connects 3 Expander (27")
ICM-HDCA-04 Connects 4 Expander (36")
ICM-HDCA-05 Connects 5 Expander (45")
ICM-HDCA-06 Connects 6 Expander (54")

Connect to Boss Bear, Bear Bones, and Baby Bear Bones.

ICM-HDCA-11	Connects 1 Expander (9"))
ICM-HDCA-12	Connects 2 Expander (18	")
ICM-HDCA-13	Connects 3 Expander (27	")
ICM-HDCA-14	Connects 4 Expander (36	")
ICM-HDCA-15	Connects 5 Expander (45	")
ICM-HDCA-16	Connects 6 Expander (54	")

DIVELBISS CORPORATION 9778 MT. GILEAD RD. FREDERICKTOWN, OH 43019 (800) 245-2327 Document Number: ds2000-0008

Page 5 of 5

web: http://www.divelbiss.com email: divelbiss@divelbiss.com

Specifications Subject to change without notice